



NOTE:  
IF EXISTING PIPE IS D.I.P.  
USE LONG SOLID SLEEVES  
OTHERWISE USE APPROVED  
TRANSITION COUPLINGS.

150mm DIA L=300mm  
200mm DIA L=400mm  
300mm DIA L=580mm  
400mm DIA L=800mm

- 24 HOUR ADVANCE NOTICE TO ALL AFFECTED RESIDENTS
- DISINFECT PIPE PER AWWA STANDARDS
- SEE GENERAL NOTES AND BEDDING DETAIL
- RESTRAIN ENTIRE LENGTH OF PIPES
- 450 mm MINIMUM SEPARATION BETWEEN PIPES
- SAMPLING TAP REQUIRED IF THERE ARE NO HOUSES OR HYDRANTS TO FLUSH IN SHUT DOWN AREA (TO BE ABANDONED AFTER TEST)

**PIPE LOWERING DETAIL**